# MIDAS®-M SILANE GROUP (SIH<sub>4</sub> SI<sub>2</sub>H<sub>6</sub>)

### **Smart Sensor Specifications**

Bringing new visibility, reliability, and ease-of-use to gas detection in semiconductor processing and industrial manufacturing.

SILANE (SiH <sub>4</sub> )
MMS-X2
3 electrode electrochemical cell
SiH <sub>4</sub> 0 ppm to 20 ppm
2.5 ppm (rising)
5 ppm (rising)
<±5% of measured value Exposure to SiH <sub>4</sub> 10 ppm for 5 minutes
Typical 5 seconds
24 months under typical application conditions
0°C to 40°C (32°F to 104°F)
<±0.04 ppm/°C <±0.8% of measured value/°C
10% RH to 90% RH
<±0.005 ppm/% RH <±2% of measured value/% RH
90 kPa to 110 kPa
No effect in typical application
<±2% ppm/year <10% of measured value/year
Silane (2.5 ppm to 7.5 ppm, default 10 ppm)
Silane (10 ppm)
<20 minutes
5°C to 25°C (41°F to 77°F)

The sensor data listed is based on the test data under normal lab test conditions (20°C to 25°C, 0% RH to 60% RH, normal atmosphere pressure); observed performance may vary based on the actual monitoring system and the sampling conditions employed.



## Midas®-M Silane Group (SiH<sub>4</sub> Si<sub>2</sub>H<sub>6</sub>) Specifications

#### **OTHER DETECTABLE GASES**

The following additional gases can be detected with this sensor cartridge. Sensor performance and characteristics will be representative of the data as tabulated above. Consult the Technical Manual to set up the Midas®-M transmitter with the designated identification code for each of the following gas types:

DETECTABLE GAS	CHEMICAL FORMULA	MEASURING RANGE
Disilane	Si <sub>2</sub> H <sub>6</sub>	0 ppm to 20 ppm

#### **CROSS SENSITIVITIES**

Each Midas-M sensor is potentially cross sensitive to other gases and this may cause a gas reading when exposed to other gases than those originally designated. The table below presents typical readings that will be observed when a new sensor cartridge is exposed to the cross sensitive gas (or a mixture of gases containing the cross sensitive species).

NOTE: The cross sensitivity data shown below does not form part of the product specification and is supplied for guidance only. Values quoted are based on tests conducted on a small number of sensors and any batch may show significant variation.

CHEMICAL FORMULA	CONCENTRATION APPLIED (ppm)	READING (ppm SIH <sub>4</sub> )
NH <sub>3</sub>	100	0
AsH <sub>3</sub>	1	0.54
CO	2000	0.56
$Cl_2$	5	-0.86
$B_2H_6$	1	0.75
C <sub>2</sub> H <sub>5</sub> OH	500	0
H <sub>2</sub>	5000	0.45
HCI	12.5	2.1
HF	10	0
H <sub>2</sub> S	10	2.7
C <sub>3</sub> H <sub>7</sub> OH	2000	0
NO <sub>2</sub>	6	-0.89
PH <sub>3</sub>	1	1.13
SO <sub>2</sub>	50	3.5
	FORMULA  NH <sub>3</sub> AsH <sub>3</sub> CO  Cl <sub>2</sub> B <sub>2</sub> H <sub>6</sub> C <sub>2</sub> H <sub>5</sub> OH  H <sub>2</sub> HCI  HF  H <sub>2</sub> S  C <sub>3</sub> H <sub>7</sub> OH  NO <sub>2</sub> PH <sub>3</sub>	FORMULA       APPLIED (ppm) $NH_3$ 100 $AsH_3$ 1 $CO$ 2000 $Cl_2$ 5 $B_2H_6$ 1 $C_2H_5OH$ 500 $H_2$ 5000 $HCI$ 12.5 $HF$ 10 $H_2S$ 10 $C_3H_7OH$ 2000 $NO_2$ 6 $PH_3$ 1

#### **HONEYWELL SAFETY PRODUCTS**

#### Americas

Honeywell Analytics 405 Barclay Boulevard Lincolnshire, IL 60069 Tel: +1 847 955 8200 Toll free: +1 800 538 0363 Fax: +1 847 955 8208 detectgas@honeywell.com

#### Europe, Middle East, and Africa

Life Safety Distribution AG (LSD) Javastrasse 2 8604 Hegnau Switzerland Tel: +41 (0)44 943 4300 Fax: +41 (0)44 943 4398 gasdetection@honeywell.com

#### Asia Pacific, India

Honeywell Analytics Asia Pacific, Co., Ltd. 7F SangAm IT Tower 434 Worldcup Buk-ro, Mapo-gu Seoul 03922 South Korea Tel: +82 (0)2 6909 0300

Fax: +82 (0)2 2025 0388 India Tel: +91 124 4752700 analytics.ap@honeywell.com

#### Mainland China

Honeywell Industrial Safety Gas Detectors Building#1, 555 Huanke Road Zhang Jiang Hi-Tech Park Pudong New Area Shanghai 201203, China Tel: 021-80386800 Fax: 021-60246070 gaschina@honeywell.com

#### Taiwan

Honeywell Taiwan Ltd 6F-2, No.8, ZiQiang S. Road, Jubei City, 30264 Taiwan Tel: +886-3-5169284

Tel: +886-3-5169284 Fax: +886-3-5169339 analytics.tw@honeywell.com Manuals and other information about this product are available at:
www.honeywellanalytics.com/en/products/



THE FUTURE IS WHAT WE MAKE IT

